

# Maxi-Cell™

Nominal Size W x H x D	SBM Double Header Part #	MERV	Initial Resistance @2000 CFM	Initial Resistance @2500 CFM
<b>Standard Capacity</b>				
24x24x12	111-700-001	14	.54	.75
24x12x12	111-700-002	14	.54	.75
24x24x6	111-700-003	14	.54	.75
24x12x6	111-700-004	14	.54	.75
20x20x5	111-700-005	14	.54	.75
24x24x12	111-701-001	11	.42	.58
24x12x12	111-701-002	11	.42	.58
24x24x6	111-701-003	11	.42	.58
24x12x6	111-701-004	11	.42	.58
20x20x5	111-701-005	11	.42	.58
<b>High Capacity</b>				
24x24x12	111-702-001	14	.59	.79
24x12x12	111-702-002	14	.59	.79
24x24x6	111-702-003	14	.59	.79
24x12x6	111-702-004	14	.59	.79
20x20x5	111-702-005	14	.59	.79
24x24x12	111-703-001	11	.44	.60
24x12x12	111-703-002	11	.44	.60
24x24x6	111-703-003	11	.44	.60
24x12x6	111-703-004	11	.44	.60
20x20x5	111-703-005	11	.44	.60
<b>Standard Capacity</b>				
24x24x12	111-710-001	14	.54	.75
24x12x12	111-710-002	14	.54	.75
24x24x6	111-710-003	14	.54	.75
24x12x6	111-710-004	14	.54	.75
20x20x5	111-710-005	14	.54	.75
24x24x12	111-711-001	11	.42	.58
24x12x12	111-711-002	11	.42	.58
24x24x6	111-711-003	11	.42	.58
24x12x6	111-711-004	11	.42	.58
20x20x5	111-711-005	11	.42	.58
<b>High Capacity</b>				
24x24x12	111-712-001	14	.59	.79
24x12x12	111-712-002	14	.59	.79
24x24x6	111-712-003	14	.59	.79
24x12x6	111-712-004	14	.59	.79
20x20x5	111-712-005	14	.59	.79
24x24x12	111-713-001	11	.44	.60
24x12x12	111-713-002	11	.44	.60
24x24x6	111-713-003	11	.44	.60
24x12x6	111-713-004	11	.44	.60
20x20x5	111-713-005	11	.44	.60

- Maxi-Cells should be installed with the pleats in vertical position.  
Each filter is labeled with filter size, safety codes, and airflow indicators to insure proper installation.
- Data listed above concerning dust holding does not account for the use of prefilters.  
Proper use of prefilters will often result in higher overall dust holding and extend the lifecycle of the Maxi-Cell final filter.
- Maxi-Cell filters are U.L. rated
- Product design and specification are subject to change without notice.